LANactive Industry Solution for Smart Grids







LANactive Industry Solution for Smart Grids

Nexans' premium high-tech networking solutions have proven their reliability in countless applications worldwide. We offer over 30 years of experience in research, development and production of Fibre To The Office (FTTO) Switches and Industrial Ethernet Switches.


IEC 61850 KEMA/ DNV-GL Certified

Nexans Industrial Ethernet Switches are compliant with the requirements of the IEC 61850 standard (parts 6, 7-1, 7-2, 7-3, 7-4, 8-1, 9-1, 9-2, including MMS and GOOSE). These communication functionalities have been tested and certified by KEMA/DNV-GL.

IEC 61850 communication requirements are applied to all parts and products of power utilities, including end devices, control equipment, data network and SCADA. This enables the building of a modern and reliable infrastructure using standardized equipment from different vendors.

LANactive Industry Solution Benefits

- Designed for Smart Grids
- Highest network availability based on advanced redundancy features
- Highest network security
- Easy maintenance
- Proven interoperability with 3rd party vendors
- High power budget for PoE+ (IEEE802.3at)
- Highest quality standards Made in Germany



SCADA

Smart Metering

Controllers

Protection Units



HSR/PRP Redundancy

HSR and PRP redundancy features are strongly advised by the IEC 61850 standard for the protection of digital communications applications among Smart Grids and provision of 'zero reconfiguration time' as well as 'zero packet loss' – at the station and process bus, for example.

Product Range

Switches

- Robust DIN-rail mounted Industrial Ethernet Switches
- Excellent performance in harsh environments (-40...+85°C, EMC, IEC 61850-3, etc.)
- Wide range of accessories: power supplies, SFP transceivers, mounting accessories etc.

Cabling

- Wide range of industrial grade copper and fibre products for your cabling infrastructure
- DIN rail-mounted copper and fibre patch panels and accessories

LANactive Manager – Network Management Tool

- Configuration and management platform for all Nexans switches
- LANactive Controller for SDN based switch configuration

Services

- 5 year warranty for industrial switches
- First class support services

Security Security IP Cameras (IP) IP Telephony



Wireless



Laptops & PCs

Offices

Nexans Advanced Networking Solutions

Bonnenbroicher Str. 2-14 41238 Moenchengladbach Germany Tel: +49 (0)2166 27-2220 Fax:+49 (0)2166 27-2499

Nexans Cabling Solutions

Alsembergsesteenweg 2, b3 B-1501 Buizingen Belgium Tel: +32 (0)2 363 38 00 Fax: +32 (0)2 365 09 99

Nexans Cabling Solutions France

4 Allée de l'Arche 92070 Paris La Défense Cedex France

Nexans Middle East

Office 1703, Jumeirah Bay Tower - X3 Jumeirah Lake Towers PO Box 634339, Dubai - UAE Tel: +971 4 369 7007 Fax: +971 4 368 9258

www.nexans.com/ans

info.ans@nexans.com

