GigaSwitch V5 7 Port 54VDC MED Series

Contact

Nexans LAN Systems Tel.: +49 (0) 2166 27 2220 sales.ans@nexans.com

LANactive 7 Port Managed Full Gigabit Ethernet FTTO Switch

- 3 Uplink Ports (2x SFP and 1x RJ45)
- 4 Isolated User Ports (4kV and 2MOPP)
- Efficient Energy Management
- Memory Card Slot
- Input Voltage Range 46 ... 57V DC

Description

Nexans LANactive GigaSwitch V5 MED series is designed for the installation in Fibre to the Office (FTTO) networks. The latest generation of FTTO switches is equipped with a state-of-the-art network processor and provides enhanced performance, security and redundancy functionality.

Galvanic Isolation

The GigaSwitch V5 MED series is equipped with integrated network isolators at the user ports to have a minimum withstand voltage of 4 kV and 2 MOPP according to EN60601-1. They prevent unwanted voltage differences between devices over the network cabling connected to the user ports.

7 Port Version

The GigaSwitch version with seven ports is part of the latest V5 series. This special variant with three uplink ports allows a redundant connection of the GigaSwitche via fibre optic. The RJ45 uplink can be used for connecting an additional Wireless LAN Access Point. All uplinks support Link Aggregation for providing redundancy and double bandwidth up to 2Gbps.

Snap-In Installation

The very compact design of the GigaSwitch allows a tool-less snap-in installation into the standard 45 mm cable duct systems or floor boxes without special mounting accessories.

Memory Card

The optional memory card automatically saves the complete current configuration and firmware of the device. In case of failure, this feature allows an easy exchange of the hardware without additional configuration. In addition, each memory card can be delivered with its own MAC address that is adopted by the switch.

Switch Management and Zero-Touch Configuration

Nexans LANactive Manager allows a simple and secure configuration of all device parameter of the GigaSwich series. With the LANactive Manager a larger number of GigaSwitches can be managed and monitored at the same time. In combination with Nexans Zero-Touch Configuration, the LANactive Manager allows automatic distribution of configurations and firmware updates. A pre-configuration of the switches is not necessary.





Standards

IEC 60601-1

IEEE 802.3

IEEE 802.3u IEEE 802.3ab

IEEE 802.3z

IEEE 802.3x

IEEE 802.1AB

IEEE 802.1D IEEE 802.1Q

IEEE 802.1X

IEEE 802.1AX

IEEE 802.3ad



Real-Time OS Yes



PoE/PoE+



Compact desi 45x90mm



Yes



Fast Installation



Redundancy



Operating Temperature 0 ... 45 °C



Electromagnetic Shielding



GigaSwitch V5 7 Port 54VDC MED Series Nexans LAN Systems Tel.: +49 (0) 2166 27 2220

Contact

Nexans LAN Systems sales.ans@nexans.com

Hardware Features

| Ordering Information | GigaSwitch V5 TI 54VD0 | P(PSE+) SFP-2VI C MED | GigaSwitch V5 TF ME | |
|--|---|--------------------------|------------------------|-------------|
| Article Number | 88303611 | 88313611 | 88303612 | 88313612 |
| Switching Type | Store-and-Forward, self-learning | | | |
| Non-blocking Switching Capacity | 20Gbps | | | |
| Packet Forwarding Rate | 2x 1.488Mpps per port | | | |
| Max. Frame Size | 9,600Bytes | 10,240Bytes | 9,600Bytes | 10,240Bytes |
| Packet Buffer | 512kBytes | 256kBytes | 512kBytes | 256kBytes |
| MAC-Address Table | 8k | 16k | 8k | 16k |
| Interfaces | | | | |
| User Ports (RJ45) | 4x 1000Base-T | | | |
| Uplink Ports (SFP)* | 2x 1000Mbps | | | |
| Uplink Ports (RJ45) | 1x 1000Base-T | | | |
| RJ45 Ports | Auto-Negotiation, MDI/MDI-X Auto-Cross Over and Auto-Polarity | | | |
| Digital Diagnostics Monitoring Interface | Yes | | | |
| Twisted Pair Cable Diagnostic | Yes | | | |
| Rotatable Head Module | Yes | | | |
| Power over Ethernet | | | | |
| Number of PoE User Ports | | - | | |
| Number of PoE Uplink Ports | 1x PSE(PoE+) acc. to IEEE802.3at - | | | |
| PoE Mode | 30W per Port, Mode A, Pin 1-2/3-6 - | | | |
| Max. PoE power budget | 30W - | | | |
| General | | | | |
| Dimensions [W x H x D] | 90mm x 45mm x 69mm | | | |
| Installation Depth | 35mm | | | |
| Material | zinc diecasting / stainless steel | | | |
| Colour | Pure White, like RAL 9010 | | | |
| Ambient Temperature | Operation: 0 45°C, Storage: -20 85°C | | | |
| Relative Humidity | 20 90% (non-condensing) | | | |
| Weight | 290g | | | |
| MTBF | > 750,000h | | | |
| Power Supply | | | | |
| Input Voltage | 46 57V DC (typ. 54V DC) | | | |
| Power Consumption | 4.3W typ., 5.5W max. | | | |
| Heat Output | 19Btu(IT)/h | | | |
| Connector | 3-pin connector (up to 2.5mm²) / (+) (-) (FPE) | | | |
| CE - Conformity | | | | |
| Electro Magnetic Capability Directive | 2014/30/EU | | | |
| Low Voltage Directive | • | | | |
| RoHS 2 | 2011/65/EU | | | |
| Engineering Standards | EN 62368-1, EN 55032, EN 55024, EN 50581 | | | |
| | | | | |



GigaSwitch V5 7 Port 54VDC MED Series

Contact

Nexans LAN Systems Tel.: +49 (0) 2166 27 2220 sales.ans@nexans.com

Software Features

Switching Parameters

VLANs IEEE802.1q with up to 256 Groups

Quality of Service Layer 2 IEEE802.1p Class of Service (4 Queues per Port)

Quality of Service Layer 3 RFC2474/3168 DSCP (4 Queues per Port)

Bandwidth LimitationBitrateEnergy Efficient EthernetIEEE802.3azFlow ControlIEEE802.3x

Fabric Attach Basic Fabric Attach Client Support

Management On-Board High-Performance Management

LEDs Management, Port Status and Activity, Memory Card

Zero-Touch Configuration Via LANactive Manager Controller

IP-AddressIPv4, IPv6DHCP-ClientDHCP, DHCPv6

DHCP Relay Agent Yes
File Transfer TFTP, SCP

Console Port V.24 with Nexans Console Cable

Web-Interface HTTP, HTTPS
Command Line Interface SSH, Telnet, V.24

Scripting Yes
SNMP SNMPv1, v2c, v3
Syslog Yes

Discovery Protocols LLDP (IEEE802.1AB), LLDP-MED (ANSI/TIA-1057), CDP

Time Synchronisation SNTP
Port Statistics Detailed per Port

Redundancy

Redundancy Protocols STP, RSTP, MSTP, MRP

Link Aggregation LACP

Security

Password Protection Two Access Levels (R/W or R/O)

Authentication via Radius and TACACS+ CLI and LANactive Manager

ACL for Management Interface Up to 16 Access Control Lists

Portsecurity via MAC-Address Up to 3 predefined MAC-Addresses

Portsecurity via Radius IEEE802.1x with MAC Bypass

DHCP Snooping Yes
Loop and Broadcast Limiter Yes

Firmware Update

Configuration-/Reset Button

Dual Firmware Image

Yes / Yes

Memory Card micro SD-Card with own MAC-Address (optionally)



GigaSwitch V5 7 Port 54VDC MED Series

Contact

Nexans LAN Systems Tel.: +49 (0) 2166 27 2220 sales.ans@nexans.com

Dimensions







